

Testo Smart Probes - refrigeration set

2 x high-pressure measuring instrument testo 549i 2 x clamp thermometer testo 115i in the testo Smart Case

Compact pro measuring instrument from the Testo Smart Probes series for use with smartphones/tablets

Application-specific menus: Target superheating, superheating and sub-cooling

All necessary measuring instruments for refrigeration applications in one set

Fast and easy installation at a pressure connection or the temperature measurement location

Low refrigerant loss thanks to hoseless application

Measurement data analyzed and sent via testo Smart Probes App

Handy transport bag testo Smart Case





The compact refrigeration set contains the high-pressure measuring instrument testo 549i as well as the clamp thermometer testo 115i (two of each). In conjunction with a smartphone or tablet, the refrigeration set is ideally suited to service and error detection on air conditioning and refrigeration systems, as well as their installation. Both measuring instruments can be set up quickly and easily directly at the pressure connection or the temperature measurement location. They also make working on widely spaced measuring points considerably easier thanks to wireless connection to a Smartphone or Tablet. The measurement values of both instruments are transmitted by Bluetooth connection to the App installed on the end

device, and can be conveniently and flexibly read out. In the App, measurement parameters (such as temperature or pressure) can be deleted, added, or their order altered, with just one click. It is also possible to change the displayed measurement parameters quickly. The App also enables evaporation and condensation temperatures to be calculated automatically. All measurement data is displayed either as a chart or in table form. The measurement data log can be emailed directly as a PDF or Excel file. The handy testo Smart Case enables the measuring instruments to be conveniently transported and means that they are always to hand when they are needed.

www.testo.com



Technical data/accessories

Smart Probes - refrigeration set

testo Smart Probes refrigeration set for servicing, commissioning and error detection on air conditioning and refrigeration systems. Consists of: 2x testo 115i, 2x testo 549i, testo Smart Case (refrigeration), batteries, calibration protocol



Order no. 0563 0002



testo Smart Probes App

The App turns your smartphone/tablet into the display of up to 6 Testo Smart Probes at the same time. The operation of the measuring instruments as well as the display of the measurement values take place by Bluetooth via the Testo Smart Probes App on your smartphone or tablet – independently of the measurement location. In addition to this, you can use the App to create measurement reports, add photos and comments to these, and send them by e-mail. For iOS and Android.

	testo 115i	testo 549i		
Sensor type	NTC	Pressure		
Measuring range	-40 to +150 °C	-1 to 60 bar		
Accuracy ±1 digit	±1.3 °C (-20 to +85 °C)	0.5 % of final value		
Resolution	0.1 °C	0.01 bar		
Connection		7/16" – UNF		
Overload rel.		65 bar		
Compatability	requires iOS 8.3 or newer / Android 4.3 or newer			
	requires mobile end device with Bluetooth 4.0			
Storage temperature	-20 to +60 °C			
Operating temperature	-20 to +50 °C			
Battery type	3 micro batteries AAA			
Battery life	150 hrs	150 hrs		
Dimensions	183 x 90 x 30 mm	125 x 32 x 31 mm		
Measurable media		CFC, HFC, HCFC, N, H ₂ O, CO ₂		
Warranty	2 years			

Accessories	Order no.	
ISO calibration certificate relative pressure, 3 measurement points distributed over the entire measuring range	0520 0085	
ISO calibration certificate temperature, one-point calibration for clamp thermometer, calibration point +60 °C	0520 0072	