



Specification  
PC104/PC105  
3-Phase Socket Tester



**ELECTRICAL SPECIFICATIONS**

**Input voltage range:** 380V to 415V AC (Phase to Phase)

**Input frequency:** 50Hz

**Input current:** < 20mA

**GENERAL SPECIFICATIONS**

**Power:** From circuit under test

**Dimensions:** 131(L) x 94(W) x 54(D) mm

**Weight:** Approx 292g (without plug)

**Includes:** Instructions

**SAFETY:**

Conforms to BS EN 61010-1, CAT III 300V

Class II Double Insulation

Pollution Degree: 2

**EMC:** Conforms to BS EN 61326-1

Check out what else you can get from Martindale:

- 17th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited  
Metrohm House, Penfold Trading Estate, Imperial Way, Watford WD24 4YY, UK  
Tel: +44(0)1923 441717 Fax: +44 (0)1923 446900  
E-mail: sales@martindale-electric.co.uk  
Website: www.martindale-electric.co.uk

© 2012 Martindale Electric Company Ltd.  
Registered in England No. 3387451. E. & O.E. Document Rev1 LITPC104/105