

## Green Mode

Meet CEC Regulations & RoHS Compliance  
No Load Power Consumption less than 0.5W

## ADAPTER- 15W Wallmount / U.K.



### FEATURE

Wallmount Type	U.K.
Input Range	90~264V/47~63 Hz
Output	4.5V~24V / 0.6~3.5A( 20W max.) 2.1 x 5.5 x 12mm connector Polarity +ve centre
Efficiency	77% typical
Protection	Short circuit protection / Over Voltage Protection / Over Current Protection
Load Regulation	± 5%
Leakage Current	Less than 0.25mA
M.T.B.F.	50,000 hours min. at 25°C, full load
Cable type	UL2468 / 18AWG or 20AWG Ferrite Core (option)
Dimension: (L) x (W) x (H) mm	64 x 50 x 26.5mm
Weight (reference)	130g
APPLICATION	Broadband & Network Equipment, Wireless Products, Portable Equipment
<b>SAFETY &amp; EMI</b>	
SAFETY	CB/CE
EMI	CE Class B, Conduction & Radiation
<b>ENVIRONMENTAL</b>	
Operating Temperature	0~+40°C
Storage Temperature	-20~+60°C
Relative Humidity	(operating) 20~80% RH / ( storage ) 10~90% RH

### RULE OF THE MODEL NAME

NO	Model Name	O/P Voltage(V)	O/P Current(A)
1	SW3829	3.0	2.5
2	SW3830	3.3	2.5
3	SW3088	5.0	2.5
4	SW3831	6.0	2.3
5	SW3089	9.0	1.6
6	SW3090	12.0	1.25
7	SW3091	15	1.0
8	SW3092	24	0.65
9	SW3832	48	0.3

AC Plug : [B- UNITED KINGDOM]



CB: JPTUV-016124 / CE

ADAPTER-18W  
Wallmount / U.K.

AC-DC adapter