

Order code	Manufacturer code	Description
85-3509	n/a	FLUKE 902 TRUE RMS CLAMP METER (HVAC)

	Page 1 of 3
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

FLUKE®

Fluke 902 True RMS Clamp Meter

**Combined inspection tool for checking heating,
ventilation and air conditioning systems**



Fluke. *Keeping your world up and running.™*

Fluke Corporation
P.O. Box 9090
Everett, WA USA 98206

Fluke Europe B.V.
P.O. Box 1186
5602 BD Eindhoven
The Netherlands

For more information call:
In the U.S.A. (800) 443-5853
or Fax (425) 446-5116
In Europe/M-East/Africa
+31 (0)40 2 675 200
or Fax +31 (0)40 2 675 222
In Canada (905) 890-7600
or Fax (905) 890-6866
From other countries +1 (425) 446-5500
or Fax +1 (425) 446-5116

Visit us on the worldwide web at:
www.fluke.com

Fluke (UK) Ltd.
52 Hurricane Way
Norwich
Norfolk
NR6 6JB
United Kingdom
Tel.: (020) 7942 0700
Fax: (020) 7942 0701
E-mail: industrial@uk.fluke.nl

Visit us on the worldwide web at:
www.fluke.co.uk

© Copyright 2006, Fluke Corporation. All rights reserved.
Printed in the Netherlands 04/06
Data subject to alteration without notice.

Pub_ID: 11112-eng

Fluke 902 True RMS Clamp Meter

FLUKE®



Fluke 902

Combined inspection tool for checking heating, ventilation and air conditioning systems

The Fluke 902 expands the existing line of quality Fluke clamp meters by adding temperature and capacitance measurement capabilities for heating, ventilation and air conditioning system inspections. Thanks to its true-RMS technology and a CAT III 600V safety rating, the Fluke 902 helps technicians work safely and accurately.

- Measures resistance, capacitance, AC voltage and current (true RMS), plus DC voltage and current.
- Also measures contact temperature with a standard K-type thermocouple
- Backlit display shows actual and Min/Max measurements with display hold function
- Use the 902 for example to capture flue gas temperatures, conduct flame rod testing, and to measure start and run motor capacitors.

Specifications

Feature	Range	Accuracy
Voltage dc	0 to 600 V	1% ± 5 counts
Voltage ac (True-RMS)	0 to 600 V	1% ± 5 counts (50/60 Hz)
Current ac (True-RMS)	0 to 600 A	2.0% ± 5 counts (50/60 Hz)
Current dc	0 to 200 μA	1.0% ± 5 counts
Resistance	0 to 9999 Ω	1.5% ± 5 counts
Continuity		< = 30 Ω
Temperature	-10° to 400°C	1% ± 0.8°C
Capacitance	1μF to 1000 μF	1.9% ± 2 counts

Safety: CAT III 600 V

Power supply: 2 AA alkaline batteries

Battery life: Typical > 12 hours

Size (HxWxD): 273 mm x 108 mm x 62 mm

Weight: 0.7 kg, including battery

Three year warranty



N10140

Ordering information

Fluke-902 True RMS Clamp Meter

Includes: 2 AA alkaline batteries, 1 pair TL75 test leads, 80BK integrated DMM Temperature probe, Users manual (w/safety information), Soft carrying case

Recommended accessories



H3 Clamp Meter
Holster



TL223 Sure Grip
Electrical Test Lead Set