

# UNITED KINGDOM 3-PIN PLUG-IN POWER SUPPLY 12VDC 18WATT



## T6157ST

### Features:

- United Kingdom Fixed AC Head
- 1 Year Warranty
- Level VI Efficiency
- CE Approved



### Description:

The Stontronics Range of Class II 18watt AC/DC United Kingdom plug-in power supplies provide 18 watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications.

Specification	
Part Number	T6157ST
Input Voltage Range	90-264Vac
Input Frequency Range	47-63Hz
Input Current Rated	0.6A Max
Output Voltage Rating	+12V
Output Current Range	1.5A
Output Min Current	0A
Output Connection Type	2.1x5.5x12mm Centre Positive – Straight Angle
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 2%
Ripple & Noise	200mVp-p
Efficiency	85% Min
Over Voltage Protection	25VDC Maximum
Over Load Protection	3.5A max with auto-recovery function
Operating Temperature	0° to 40°C
Storage Temperature	-20° to +60°C
Operating Humidity	20 to 85%
Storage Humidity	5 to 95%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	Meet T-LICENSE(BS EN60950-1)
EMI Standard	Meet CE(EN55022)
MTBF	50K Hours
Size mm max.	74.5 (L) x 60 (W) x 77(H)
Weight	124 g
Regulator Type	Switched Mode Power Supply

#### General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | Stontronics Ltd  
Chancerygate Business Centre, Cradock Road, Reading RG2 0AH, UK  
t: +44 (0) 118 931 1199

# UNITED KINGDOM 3-PIN PLUG-IN POWER SUPPLY 12VDC 18WATT

T6157ST

## Diagrams

