

UNITED KINGDOM 3-PIN PLUG-IN POWER SUPPLY 18VDC 24WATT



T6369ST

Features:

- United Kingdom Fixed AC Head
- 1 Year Warranty
- Level VI Efficiency
- CE Approved



Description:

The Stontronics Range of Class II 24 watt AC/DC United Kingdom plug-in power supplies provide 24 watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications.

Specification	
RS Stock Number	T6369ST
Input Voltage Range	100-240Vac
Input Frequency Range	47-63Hz
Input Current Rated	0.8A Max
Output Voltage Rating	+18V
Output Current Range	1.33A
Output Min Current	0A
Output Connection Type	2.1x5.5x12mm Centre Positive
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 5%
Ripple & Noise	200mVp-p
Efficiency	87% Min
Over Voltage Protection	Overload conditions shall decrease the output voltage. Removal of an output overload shall provide automatic recovery for the output voltage.
Over Load Protection	2A max with auto-recovery function
Operating Temperature	0 to 40°C
Storage Temperature	-20 to +70°C
Operating Humidity	20 to 85%
Storage Humidity	10 to 95%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	Meet T-LICENSE(BS EN60950-1)
EMI Standard	Meet CE(EN55022)
MTBF	50K Hours
Size mm max.	61.6 (L) 26 (W) * 65.7 (H) mm
Weight	65g
Regulator Type	Switched Mode Power Supply

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | Stontronics Ltd
Chancerygate Business Centre, Cradock Road, Reading RG2 0AH, UK
t: +44 (0) 118 931 1199

UNITED KINGDOM 3-PIN PLUG-IN POWER SUPPLY 18VDC 24WATT

T6369ST

Diagrams

UNIT: mm
COLOR: BLACK



