

UT20B

Pocket-Size Digital Multimeters



SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	200mV/2000mV/20V/200V/300V	±(1.5%+2)
AC Voltage	200V/300V	±(2.5%+15)
DC Current	2000μA/20mA/200mA	±(2.5%+10)
Resistance	200Ω/2000Ω/20kΩ/200kΩ/2000kΩ	±(2.5%+5)
Special Functions		
Battery Test	1.5V, 9V	±(2.5%+2)
Diode		✓
Square Wave Output		✓
Low Battery Display		✓
Input Impedance for DC Voltage Measurement	Around 1MΩ	✓
Max.Display	1999	✓

GENERAL CHARACTERISTICS

Power	12V Battery A23
LCD Size	31 x 13mm
Product Colour	Red and Grey
Product Net Weight	125g
Product Size	95 x 52 x 26mm
Standard Accessories	Test Lead, Battery, English Manual
Standard Individual Packing	Blister
Standard Quantity Per Carton	80pcs
Standard Carton Measurement	568 x 378 x 320mm (0.069CBM Per Standard Carton)
Standard Carton Gross Weight	12kg

Specifications and other information are subject to change without further notice.