

UT352



Sound Level Meters

SPECIFICATIONS

Measurement Functions	UT352
Total Range	30 to 130dB
Maximum Level	130dB
Accuracy	±1.5dB
Range Selections	30 to 80dB, 50 to 100dB, 60 to 110dB, 80 to 130dB
Frequency Range	31.5Hz to 8000Hz
Frequency Weighting	A and C
Time Weighting	FAST (125ms) SLOW (1 second)
Analogue Bar Graph	30~130dB
Warning	Over-Range "OVER", Under-Range "UNDER"
Analogue Outputs	AC: 0.707Vrms full scale; Output impedance: around 600• • DC: 2Vrms full scale; 10mV/dB; Output impedance around 100• •
Max/Min Mode	✓
Data Hold	✓
Display Backlight	✓
Sleep Mode	✓
Low Battery Display	4.8V
Data Logging	63 data sets

GENERAL CHARACTERISTICS

Power	1.5V Battery (AA) x 4
LCD Size	53 x 41mm
Product Color	Red and Grey
Product Net Weight	330g
Product Size	273 x 70 x 39mm
Standard Accessories	Batteries, English Manual
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	30pcs
Standard Carton Measurement	670 x 385 x 300mm (0.077 CBM Per Standard Carton)
Standard Carton Gross Weight	18kg

Specifications and other information are subject to change without further notice.