

UT372



Tachometers

SPECIFICATIONS

Technical Specifications	UT372
Measurement	10 to 99,999 RPM
Range Selection	10 to 99 RPM, 100 to 999 RPM, 1000 to 9999 RPM, 10000 to 99999 RPM
Best Accuracy	0.04% ± 2dgt
Display	99999 counts
Target Distance	50mm to 200mm
Start/Hold	Start and Stop Measurement, Data Hold
MAX/MIN/AVE/ZERO	Maximum Value, Minimum Value, Average Value, Zeroing
Sleep Mode	Around 15 minutes
Low Battery Display	4.8V
USB	✓

GENERAL CHARACTERISTICS

Power	1.5V Battery (AA) x 4
LCD Size	53 x 41mm
Product Color	Red and Grey
Product Net Weight	100g
Product Size	184 x 56 x 34mm
Standard Accessories	Batteries, English Manual, Reflecting Tape, USB Interface Cable
Standard Individual Packing	Blister
Standard Quantity Per Carton	20pcs
Standard Carton Measurement	420 x 305 x 370mm (0.047 CBM Per Standard Carton)
Standard Carton Gross Weight	5kg