



- 900 W Hot air station for simple repair and heating tasks
- Modern and intuitive operational concept thanks to clear menu structure
- Reduced footprint thanks to stackability
- Electronical controlled temperature
- Accurate adjustment of hot air through brushless turbine
- Up to 5 pre-sets which can be automatically run in a profile
- Housing cover useable as storage
- Unit inkl. safety rest and fixed hot air iron

WTHA 1 Set

Code No.: T0053173399

Dimensions W x D x H (mm)	212 x 167 x 122 mm
Dimensions W x D x H (Inch)	8,35 x 6,57 x 4,80 Inch
Weight (ca) in kg	1,95 kg
Voltage	230 V
Power output	900 W
Channels	1
Temperature range (depends on tool) °C	50 - 600
Temperature range (depends on tool) °F	100 - 1000
Temperature accuracy °C	± 30
Temperature accuracy °F	± 54
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding	Nein
Display	Grafical backlit LC-Display
Air consumption l/min	---
Operating pressure	Na
Capacity l/min	5 - 60 l / 20°C 5 - 110 l / 300°C
Vacuum	Na