

Produkt Informationen



WDD 81V

Bestellnummer : T0053256699



Desoldering Station Set

Desoldering Station Digital 95 W, 230 V, Compressed Air or Inert Gas Operated

Technical Data

Dimensions (mm)

inch 7,1 (L) x4.53 (W)x 4,3 (H)

Mains Voltage: 230V/ 50Hz, 120 V / 60Hz

Power Consumption: 95 W

Protection Class: 1 (Control) and3 (Soldering Tool)

Fuse: T 500 mA (230V); T 1A (120 V)

Temperature Regulation: Digital 50°C - 450°C (122°Cf-842°Cf)

Precision: ± 9°C (± 17°F)

Compressed Air: Inlet pressure600 kPA (87 psi) oil-free, dry compressed air

Compressed Air Converter: Air Consumption 35 l / min; max. vacuum 55 kPA (8 psi)

Compresses Air Connection: Compressed air hose of 6 mm (0,24") external diameter

Equipotential Bonding:

via 3,5 mmjack bushing in the button of the unit. (State upon deliver y: hard grounded , plug is not inserted)