

OPEN FRAME POWER SUPPLY 15VDC 125WATT



STONTRONICS: PSF-125-15

Features:

- Universal Input
- High Efficiency
- 3 Year Warranty
- Efficiency Level VI



Description:

The 125W open frame power supply range has been specially designed to offer high efficiency, long life and high reliability for use in a variety of applications. Each model is approved to CE, CB, UL and comes with a 3 year warranty.

SPECIFICATION	
Part Number	PSF-125-15
Output Voltage	15Vdc
Output Current (Max.)	8.4A
Output Current (Min.)	0A
Power (Watts)	125W
Line Regulation	+/- 0.5%
Voltage Tolerance	+/- 5%
Ripple & Noise (mV p-p)	100mV
Protections	Over Current Protection Over Voltage Protection Short Circuit Protection
Full Input Range	90 - 264Vac
Full Input Frequency Range	47 - 63Hz
Efficiency	85%/115VAC 87%/230VAC
Input Current (RMS. Max)	1.5A
Leakage Current	<3.5mA
AC Mains Plug Inlet	LANDWIN3961P0300T (Central Pin Removed)
DC Output Connector	LANDWIN3961P0800T
Hi-Pot Specification (I.P. to O.P.)	1500Vac or 2121Vdc 10mA 1 min (Primary to Secondary GND)
Operating Temperature	-20°C to 70°C
Storage Temperature	-40°C to 85°C
Operating Humidity	20 to 90%
Storage Humidity	10 to 95%
Safety Approvals	GB4943-2001; EN60950-1: 2006
EMI Standards	EN55022(CISPR22) CLASS B
PB-free	Yes, RoHS Compliant
MTBF	100K Hours
Case Size (mm)	127 x 76 x 30.5

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


STONTRONICS

TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500

OPEN FRAME POWER SUPPLY 15VDC 125WATT STONTRONICS: PSF-125-15



Diagrams



General Note
TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.