



## 60W Soldering Iron Kit, LED Halo Ring™

Item No.: WLIRK6012A  
60W Soldering Iron Kit, LED Halo  
Ring™, 120V

Solder skillfully and confidently with Weller's 30W Soldering Iron with LED Halo Ring™. With its 360 degree illumination, ergonomic molded pencil grip handle, easy-to-change tips, and integrated safety rest, it's the perfect high-quality and versatile soldering iron for all your soldering needs.

### RECOMMENDED FOR FOLLOWING APPLICATIONS



### KEY FEATURES

- |                                 |   |
|---------------------------------|---|
| High Visibility LED Halo Ring™: | 360 degree illumination provides focused, bright light ensuring high-quality solder joints                |
| Optimal Precision and Control:  | Ergonomic molded pencil grip provides you with comfort, precision and control                             |
| Quick Tip Change:               | Easily replace worn tips or change tip applications   |
| Versatile:                      | Full range of tip designs – conical, chisel or screwdriver – perfect for intricate soldering applications |
| Integrated Safety Rest:         | On-board safety rest holds iron when not in use, reducing the risk of injury or damage to your workspace  |



**Versatile**

Full range of tip designs – conical, chisel or screwdriver – perfect for intricate soldering applications



**High Visibility LED Halo Ring™**

360 degree illumination provides focused, bright light ensuring high-quality solder joints



**Optimal Precision and Control**

Ergonomic molded pencil grip provides you with comfort, precision and control



**Quick Tip Change**

Easily replace worn tips or change tip applications

**Integrated Safety Rest**

On-board safety rest holds iron when not in use, reducing the risk of injury or damage to your workspace

**TECHNICAL DATA**

Voltage	120 V
UPC	037103346490
Minimum Order Quantity	1
Weight in lb	0.726
CE	✓
Temperature range °C	427
Weight in g	330
Cord Length	1.50
Tip Size	6.4mm
Tip shape	Chisel
Power cable	USA
Power	60 W
Temperature range °F	880