

# Product information

## 7.2V Pencil Drill Driver



### DF012DSE

Battery Type	Lithium-ion
Battery Ah	1.5 Ah
Voltage	7.2 v
Battery Quantity	2
Max. in steel	5 mm
Max. in wood	6 mm
Drive shank Hex	1/4 "
Noise sound pressure	70 dB(A)
Noise K factor	3 dB(A)
No Load Speed (Hi)	650 rpm
No Load Speed (Lo)	200 rpm
Max Torque S/H	3.6 / 5.6 Nm
Torque Settings	21 + drill
Vibration: Drilling	2.5 m/sec <sup>2</sup>
Vibration K factor	1.5 m/sec <sup>2</sup>
Net weight	0.53 kg



**STANDARD EQUIPMENT:** 198000-3 7.2V Li-ion Battery , DC10WA 7.2V-10.8V BATTERY CHARGER, Phillips bit, Carry case

- Forward/reverse rotation
- 2-speed selection (High/Low)
- LED job light
- Operates in straight or pistol grip positions
- Ergonomic soft grip
- Auto-stop system (on detection of remaining battery power):  
Indication lamp warns user visually of battery power reduction when it reduces to a certain low level. If battery power reduces further, the motor automatically stops to prevent incomplete fastening.
- Auto-stop clutch: The motor automatically stops at the moment when the clutch is disengaged.

Details correct as of: 27-10-2017

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)