

Product information

13mm PERCUSSION DRILL



Satisfying the professional's needs

HP1640K

Max. in masonry	16 mm
Max. in steel	13 mm
Blows per minute	0-44800 bpm
Max. in wood	30 mm
Vibration drilling	2.5 m/sec ²
Vibration hammer drilling	19 m/sec ²
No load speed	0 - 2800 rpm
Input wattage	680 w
Vibration K factor	2 m/sec ²
Noise sound power	103 dB(A)
Noise sound pressure	92 dB(A)
Noise K factor	3 dB(A)
Net weight	2.0 kg



Details correct as of: 16-1-2012

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com