

Product information

ORBITAL ACTION JIGSAW



Satisfying the professional's needs

4329

Vibration cutting sheet metal	5 m/sec ²
Vibration cutting wood	7 m/sec ²
Max in steel	6 mm
Input wattage	450 w
Vibration K factor	1.5 m/sec ²
Noise sound power	94 dB(A)
Noise sound pressure	83 dB(A)
Noise K factor	3 dB(A)
Max in wood	65 mm
Net weight	1.9 kg
Stroke Length	18 mm
Strokes per minute	500-3100 spm



- Compact & Lightweight
- Variable speed control
- Dust extraction facility
- Chip deflector
- Sturdy adjustable base

Details correct as of: 16-1-2012

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com