10 Port USB C Fast Charger

TIGER PART: TGR-10P-USB-C

#### Features:

- 10 ports x 2.1 amp fast charging outputs
- 100-240 vacinput
- Charge multiple device and sync data at the same time
- Max. Data transfer rate 480Mbps


















The Tiger Power range of industrial USB chargers are safety approved and highly reliable, meeting latest level VI energy efficiency legislation. The TGR-10P-USB-C model has 10 ports, allowing for an office or classroom to charge and sync their device at the same time via the 2.1 amp outputs. Suitable for a wide range of applications.

Part number supplied with UK mains cable, data cable and PSU:	TGR-10P-USB-C
Part number (No UK cable or power supply) :	TGR-10P-USB-C-NCP
Part number (European cable):	TGR-10P-USB-C-EU
Input voltage:	220-240vac (230vac nominal)
Input frequency:	50Hz
Output voltage:	5vdc
Current:	2.1 amps max. x 10 ports
Power:	10 Ports x 2.1A max. Fast Charging (120W max)
Powered by:	Internal high quality power supply (supplied)
Dimensions:	193 x 80.3 x 24.3mm
Weight:	1100g
AC cord length (where supplied):	1.8 metres
DC cord length:	Not applicable
DC connector:	USB type C
Polarity:	Standard
Efficiency:	89%
Input current RMS Max.:	2.0A
Inrush Current at 230vac:	120A max. at 220vac cold start, max. load
Load regulation:	+ / - 5%
Safety approval:	62368-1
M.T.B.F:	50,000 hours (MIL-HDBK-217F) at 25 degrees C
Operating temperature:	0°C to + 40°C

### TIGER POWER PRODUCTS - QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.

# 10 Port USB C Fast Charger



## TIGER PART: TGR-10P-USB-C





TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.