INTERNATIONAL- 48V 0.5A 24W



PART: TGR-PT-24W-48-INT

Features:

- Built in Over Current, Short Circuit & Over Voltage Protections
- Universal 100-240vac input voltage
- Supplied complete with 4 Interchangeable AC pins
- Level VI efficiency
- Approved to latest 62368-1 world safety standards including
- Chinese plug also available as optional extra
- Compact Housing Dimensions 75 x 36 x 66mm



The Tiger Power range of switch mode power supplies feature full safety approvals to latest 62368-1 standards and also level VI energy efficiency requirements. The TGR-PT-24W-48-INT 48vdc 0.5A amp model provides a reliable constant voltage output at up to 24 Watts continuous, suitable for a wide range of applications.

TGR-PT-24W-48-INT
TGR-PT-24W-48-INT-UKEU
TGR-PT-24W-48-INT-UKEUUS
100-240vac (90-264vac max.)
47 - 63Hz
48vdc
0.5A
24 Watts
Short Circuit, Over Voltage, Over Current protection
75 x 36 x 66mm
158g (body only)
0.1W max.
1.5 metres
2.1 x 5.5 x 12mm (Female) Other options on request
+ve (positive) centre
88%
1.5A
40A max.
+ / - 5%
62368-1 including UL (USA), CE and C-Tick.
300,000 hours (Telcordia SR-332) at 25 Degrees C
0°C to + 40°C


TIGER POWER PRODUCTS - QUALITY & RELIABILITY


This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.

INTERNATIONAL- 48V 0.5A 24W



PART: TGR-PT-24W-48-INT





TIGER POWER PRODUCTS - QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.