

RF REMOTE CONTROLLERS



Features:

- Reliable RF Signal
- No Line of Sight needed (as with Infra Red Controllers)
- Complete Range to Choose from including Single Colour & RGB options
- Suitable for use with a wide range of LED lighting including LED strip



Part TGR-REM-SC-RF-1

12V – 24V input & Output
 Dimensions 110 x 56 x 34mm
 Single Channel 8A
 Brightness Adjust and ON/OFF



Part TGR-REM-WIFI

Free App for iOS & Android
 Dimensions 53 x 24 x 11mm
 5V – 24V 96W (5A max.)
 Quick Connect 2.1mm in/out



Part TGR-REM-SC-RF-2

12V – 24V input & Output
 6A x 3 Channels 18A MAX.
 (216W / 12V 432W / 24V)
 Up to 20M Control Distance



Part TGR-REM-SC-RF-3

Colour Temp Adj
 30A 2700 – 6500K
 5V – 24V2 Channel



Part TGR-REM-SC-RF-4

5V – 24V input & Output
 5A Max. Output Current.
 8 Dynamic Effects
 10 Step Dimming



Part TGR-REM-SC-RF-5

12V – 24V input & Output
 30A MAX.
 On Off and Brightness Adjust
 8 Dynamic Effects



Part TIG-REM-RGB-RF

12 – 24vdc input & Output (Input voltage will equal the output voltage so if you want to control 12V LED strip please provide a 12V Input)
 12A Maximum current
 24 Button RF Remote for RGB Full Colour Control
 Adjust Brightness levels and Colour- ON/OFF control

TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.