

# RF REMOTE CONTROLLERS



## Features:

- Reliable RF Signal
- No Line of Sight needed (as with Infra Red Controllers)
- Complete Range to Choose from including Single Colour & RGB options
- Suitable for use with a wide range of LED lighting including LED strip



### Part TGR-REM-SC-RF-1

12V – 24V input & Output  
 Dimensions 110 x 56 x 34mm  
 Single Channel 8A  
 Brightness Adjust and ON/OFF



### Part TGR-REM-WIFI

Free App for iOS & Android  
 Dimensions 53 x 24 x 11mm  
 5V – 24V 96W (5A max.)  
 Quick Connect 2.1mm in/out



### Part TGR-REM-SC-RF-2

12V – 24V input & Output  
 6A x 3 Channels 18A MAX.  
 (216W / 12V 432W / 24V)  
 Up to 20M Control Distance



### Part TGR-REM-SC-RF-3

Colour Temp Adj  
 30A 2700 – 6500K  
 5V – 24V2 Channel



### Part TGR-REM-SC-RF-4

5V – 24V input & Output  
 5A Max. Output Current.  
 8 Dynamic Effects  
 10 Step Dimming



### Part TGR-REM-SC-RF-5

12V – 24V input & Output  
 30A MAX.  
 On Off and Brightness Adjust  
 8 Dynamic Effects



### Part TIG-REM-RGB-RF

12 – 24vdc input & Output (Input voltage will equal the output voltage so if you want to control 12V LED strip please provide a 12V Input)  
 12A Maximum current  
 24 Button RF Remote for RGB Full Colour Control  
 Adjust Brightness levels and Colour- ON/OFF control

## TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.