



## ANSMANN IL300R

Years Warranty\*

Rechargeable work light for professional use, with multi-functions, robust housing and very bright

### Features

- Professional work light with latest SMD LED technology
- Additional spotlight in lamp head
- Robust plastic housing with rubberized surface
- 180° rotatable lamp handle, (in 8 steps), for flexible lighting alignment
- Two foldable and 360° rotatable hooks at the back
- Two magnets at the back of the housing and one magnet at the bottom of the handle
- Impact protected Li-Ion battery pack (3.7V / 2500mAh)
- Charging via supplied USB cable
- Charge control indication via duo LED
- Charging time: approx. 3,5 hours
- 2 years ANSMANN Germany warranty

Mode	Light range	Luminous flux	Brightness	Operating time
Main LED 100%	30 m	600 lumens	1.120 Lux	3 h
Main LED 50%	22 m	300 lumens	570 Lux	6 h
Additional LED	55 m	120 lumens	3.200 Lux	10 h



Luminous flux



Brightness



Operating time




Magnetic mounting



Hanging Hook



Rechargeable Li-Ion battery



Input USB Type C



360° rotatable



Article number: 1600-0152

Product content: Working light, USB-C charge cable, operating instructions



## Specifications

Nominal voltage	3,7 V				
Nominal capacity	2500 mAh				
Illuminant	<b>Mode</b>	<b>Illuminant</b>	<b>Illuminant power</b>	<b>Optical system</b>	<b>Colour temperature</b>
	Main LED	6× LED	6 W	Wide angle illumination	6500 - 7000 K
	Additional LED	LED	1 W	Point Focused	6000 K
Illuminant power	6 W				
Light range	55 m				
Luminous flux	600 lumens				
Brightness	3.200 Lux				
Protection class	IP20				
Operating time	10 h				
Power supply	Li-Ion battery pack (3.7V / 2500mAh)				
Performance data	<b>Mode</b>	<b>Light range</b>	<b>Luminous flux</b>	<b>Brightness</b>	<b>Operating time</b>
	Main LED 100%	30 m	600 lumens	1.120 Lux	3 h
	Main LED 50%	22 m	300 lumens	570 Lux	6 h
	Additional LED	55 m	120 lumens	3.200 Lux	10 h
Color	black				
Packaging	cardboard box				
Operating temperature	-20 - 25 °C				

Storage temperature

-20 - 30 °C