



JAHRE
YEARS
GARANTIE
WARRANTY
2

ANSMANN IL300R

- Professional work light with latest SMD LED technology
- Additional spotlight in lamp head
- Robust plastic housing with rubberized surface
- 180° rotatable lamp handle, (in 8 steps), for flexible lighting alignment
- Two foldable and 360° rotatable hooks at the back
- Two magnets at the back of the housing and one magnet at the bottom of the handle
- Impact protected Li-Ion battery pack (3.7V / 2500mAh)
- Charging via supplied USB cable
- Charge control indication via duo LED
- Charging time: approx. 3,5 hours
- 2 years ANSMANN Germany warranty

Mode	Light range	Luminous flux	Brightness	Operating time
Main LED 100%	30 m	600 lumens	1.120 Lux	3 h
Main LED 50%	22 m	300 lumens	570 Lux	6 h
Additional LED	55 m	120 lumens	3.200 Lux	10 h

INFORMATION

Product name	IL300R
Part No.	1600-0152
EAN code	4013674106004
Customs tariff number	85131000000
Material Group	02
Product content	Working light, USB-C charge cable, operating instructions

Product	63,9 × 40,3 × 274 mm / 312 g
Packing + Product	125 × 50 × 307 mm / 464 g
Packing Unit	4 Pieces (318 × 137 × 215 mm)

