

# EPN7582NHG

## 750W Planer

### Features

- Ideal for flattening and smooth rough wood surfaces
- 3 chamfering grooves (0.5,1,1.5mm) in die-cast front shoe for added precision
- Double sided fence for precision planing
- Overmould dust extraction switch for left or right port
- Full length trigger with overmould for greater control
- DustTech™ Integrated dust technology system for maximum pick-up efficiency
- Livetool Indicator™ glows blue when plugged into power supply



SPECIFICATION (1)	EPN7582NHG
Sound pressure level (dB(A))	103
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	96
Sound power level uncertainty [dB[A]]	3
Vibration level [m/s <sup>2</sup> ]	3
Vibration uncertainty [m/s <sup>2</sup> ]	1.5
No load speed (rpm)	16,000
Supplied in	Kitbox
No. of batteries supplied	0
Article Number	5133000353
Weight (kg)	3.2
Power input (W)	750
Rebate depth (mm)	0-12
Planing width (mm)	82
Planing depth (mm)	2