

R18CS-0

Features

- Ideal for making long straight cuts, trimming sheet wood to size, cutting kitchen work tops, flooring or to make quick and accurate cross cuts in timber.
- Impressive cut capacities 52mm at 90°, 36mm at 45° allows you to complete applications usually reserved for corded tools
- Tool less depth and bevel adjustments make it quick at easy to set up the saw
- Rotatable dust port helps keep the cut line clear and allows you to work in a dust free environment by connecting to a vacuum
- Premium Thin Kerf 165mm blade with 24 carbide tipped teeth provides superb performance and cut quality
- Make up to 275 cross cuts in 2x4 (52x100mm) timber per charge when combined with our high capacity Lithium+ 5.0Ah battery RB18L50



SPECIFICATION (1)	R18CS-0
Bore size (mm)	16
Max. cutting depth 56 degrees [mm]	28
No load speed (rpm)	4,700
Voltage (V)	18
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Blade diameter (mm)	165
Article Number	5133002338
Bevel capacity (°)	0-56
Weight with battery pack (kg)	2.8
Blade width (mm)	1.6
Max. cutting depth 45<special id ="5" /> (mm)	36
Max. cutting depth 90<special id ="5" /> (mm)	52