

# R18JS-0

## 18V Jigsaw

### Features

- Cordless jigsaw with 25mm stroke length ideal for cutting wood at a variety of different angles
- 1 handed speed control for easy speed adjustment to suit different applications
- 4 stage pendulum action for enhanced cutting performance
- Tool-less blade clamp for quick and easy blade change
- Lock on switch keeps your tool working so reduces your fatigue
- LED worklight illuminates the cut line and work area
- Easy base adjustment to cut between 0° to 45° angles



SPECIFICATION (1)	R18JS-0
Sound pressure level (dB(A))	86
Sound pressure level uncertainty [dB[A]]	3
Sound power level measured [dB[A]]	97
Sound power level measured uncertainty [dB[A]]	3
Vibration cutting metal [m/s <sup>2</sup> ]	8
Vibration cutting metal uncertainty [m/s <sup>2</sup> ]	1.5
Vibration cutting in boards [m/s <sup>2</sup> ]	8.3
Vibration cutting boards uncertainty [m/s <sup>2</sup> ]	3
Voltage (V)	18
Battery type	–
Supplied in	Recyclable Carton
Charger supplied	–
No. of batteries supplied	0
No load stroke rate (spm)	1,100 - 3,000
Article Number	5133002158
Weight with battery pack (kg)	2.53
Max. cutting capacity wood (mm)	101
Max. cutting capacity steel (mm)	6
Stroke length (mm)	25