

EMS190DCL

18V Mitre Saw

Features

- Cordless Mitre saw cuts up to 38x108mm at 90°
- Exactline laser accurately aligns the cut line with the blade
- Pre-select mitre angles at 0,15,22.5,31.6 and 45° and bevel from 0-45°
- Thin Kerf 24T carbide tipped blade for improved performance and longer runtime
- Extremely compact and lightweight for great portability
- Make up to 189 cross cuts (22x100mm) combined with the Lithium+ 5.0Ah battery RB18L50



SPECIFICATION (1)	EMS190DCL
Voltage (V)	18
Battery pack capacity (Ah)	-
Battery type	-
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Blade type	24 tooth TCT
Blade diameter (mm)	190
Article Number	5133000932
Weight with battery pack (kg)	7.43
Mitre capacity right (<special id ="5" />)	45
Mitre capacity left (<special id ="5" />)	45
Bevel capacity left (<special id ="5" />)	45