

# R18N16G-0

## Features

- AirStrike™ Technology provides cordless convenience, eliminating the need for a noisy compressor, bulky air hose or expensive gas cartridges
- Fires 16 Gauge (1.6mm) nails from 19 to 65mm long
- 2 firing modes, full sequential mode for precision and contact actuation mode for rapid fastening
- Grip-Light technology engages LED by grasping the handle
- Tool less depth of drive adjustment helps protect work surface and allows proper setting of nail heads
- Dry-fire lockout prevents the tool working without nails loaded
- Tool less jam release for easy removal of clear nails
- Low nail indicator so you can see when it is time to re-load
- Belt hook mounts left or right side for added convenience



- includes 2 non-marring pads to keep work surface free of tool marks
- Fire up to 375 65mm nails into pine using RB18L15
- Fire up to 1000 50mm nails into pine using RB18L40
- Runtime can vary by tool, battery and application

SPECIFICATION (1)	R18N16G-0
Voltage (V)	18
Nail type (mm)	1.6
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Magazine capacity nails	100
Article Number	5133002222
Weight with battery pack (kg)	3.13
Magazine angle	Straight
Nail capacity	19-65mm