

R18N18G-0

18V Nailer

Features

- AirStrike™ Technology provides cordless convenience, eliminating the need for a noisy compressor, bulky air hose or expensive gas cartridges
 - Fires 18 Gauge (1.2mm) nails from 15 to 50mm long
 - 2 firing modes, full sequential mode for precision and contact actuation mode for rapid fastening
 - Grip-Light technology engages twin LEDs by grasping the handle
 - Tool less depth of drive adjustment helps protect work surface and allows proper setting of nail heads
 - Dry-fire lockout prevents the tool working without nails loaded
 - Tool less jam release for easy removal of clear nails
 - Low nail indicator so you can see when it is time to re-load
 - Belt hook mounts left or right side for added convenience
-
- includes 2 non-marring pads to keep work surface free of tool marks
 - Fire up to 600 50mm nails into pine using RB18L15
 - Fire up to 1600 50mm nails into pine using RB18L40
 - Runtime can vary by tool, battery and application



SPECIFICATION (1)	R18N18G-0
Sound pressure level (dB(A))	83
Sound pressure level uncertainty [dB[A]]	3
Sound power level measured [dB[A]]	94
Sound power level measured uncertainty [dB[A]]	3
Vibration level [m/s ²]	1.5
Vibration uncertainty [m/s ²]	1.5
Voltage (V)	18
Nail type (mm)	1.2
Supplied in	Recyclable Carton
Charger supplied	–
No. of batteries supplied	0
Magazine capacity brads	105
Article Number	5133002093
Weight with battery pack (kg)	2.93
Magazine angle	Straight
Nail capacity	15-50mm