

P620

18V Speed Sprayer

Features

- Ideal for painting fences, exterior walls, garage doors and outbuildings
- Choose between three spray patterns, horizontal, vertical or round, to provide you with the best coverage whilst minimising overspray
- Suitable for use with any brand paint
- Highly versatile spray system that can be used with varnishes, wood preservatives, enamels, as well as oil-based and water-based paints
- Innovative and patented delivery system also minimizes the need for dilution
- Cordless convenience means paint projects have no limits. Spray up to 4m² per minute
- GripZone™ overmould technology for improved comfort with a positive grip



SPECIFICATION (1)	P620
Sound pressure level (dB(A))	83
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	94
Sound power level uncertainty [dB[A]]	3
Vibration level [m s ²]	1.6
Vibration uncertainty [m s ²]	1.5
Voltage (V)	18
Container capacity (ml)	1000
Area flow rate sprayer (m ² /min)	4
Paint coverage sprayer (m ² /min)	10
Flow rate (l/h)	20
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Article Number	5133000155
Weight with battery pack (kg)	2.36