

RPD1200-K

1200W Percussion Drill

Features

- Variable speed forward & reverse for total control
- Compact & lightweight for easy drilling
- GripZone™ overmould for positive grip and improved comfort
- Metal gear housing
- Metal chuck with auto-spindle lock
- 2-Speed
- LED



SPECIFICATION (1)	RPD1200-K
Sound pressure level (dB(A))	108
Sound pressure level uncertainty [dB[A]]	3
Sound power level [dB[A]]	109.5
Sound power level uncertainty [dB[A]]	3
No load speed gear 1 (rpm)	0-1,200
No load speed gear 2 (rpm)	0-3,200
Chuck type	Keyless
Supplied in	Kitbox
Charger supplied	–
percussion rate gear 1	0-19,200
percussion rate gear 2	0-51,200
Article Number	5133002068
Weight (kg)	3.15
Power input (W)	1200
Max drilling steel (mm)	8/16
Max. drilling wood (mm)	25/50
Max. drilling masonry (mm)	18/22
Chuck capacity (mm)	13