

# RPD800-K

## 800W Percussion Drill

### Features

- Variable speed forward & reverse for total control
- Compact & lightweight for easy drilling
- Gripzone™ overmould for positive grip and improved comfort
- Single sleeve (auto spindle lock) chuck
- LED



SPECIFICATION (1)	RPD800-K
Sound pressure level (dB(A))	96
Sound pressure level uncertainty [dB[A]]	3
Sound power level measured [dB[A]]	107
Sound power level measured uncertainty [dB[A]]	3
Vibration screw driving [m s <sup>2</sup> ]	1
Vibration screw driving uncertainty [m s <sup>2</sup> ]	1.5
Vibration drilling into Metal [m s <sup>2</sup> ]	3.9
Vibration drilling into metal uncertainty [m s <sup>2</sup> ]	1.5
Vibration drilling into concrete [m s <sup>2</sup> ]	15.6
Vibration drilling into concrete uncertainty [m s <sup>2</sup> ]	1.5
No load speed gear 1 (rpm)	0-3,000
Chuck type	Keyless
Max. percussion rate (bpm)	0-51,000
Supplied in	Kitbox
Charger supplied	-
Article Number	5133002019
Weight (kg)	1.8
Power input (W)	800
Max drilling steel (mm)	13
Max. drilling wood (mm)	34
Max. drilling masonry (mm)	16
Chuck capacity (mm)	13