

RPD500-G

500W Percussion Drill

Features

- Variable speed forward & reverse for total control
- Compact & lightweight for easy drilling
- GripZone™ overmould for positive grip and improved comfort



| SPECIFICATION (1) | RPD500-G |
|--|------------|
| Sound pressure level (dB(A)) | 95 |
| Sound pressure level uncertainty [dB[A]] | 3 |
| Sound power level measured [dB[A]] | 106 |
| Sound power level measured uncertainty [dB[A]] | 3 |
| Vibration drilling into concrete [m/s ²] | 15.6 |
| Vibration drilling into concrete uncertainty [m/s ²] | 1.5 |
| No load speed gear 1 (rpm) | 3,000 |
| Chuck type | Keyless |
| Supplied in | Gift box |
| Charger supplied | – |
| percussion rate gear 1 | 0-50,000 |
| Article Number | 5133002244 |
| Weight (kg) | 1.6 |
| Power input (W) | 500 |
| Max drilling steel (mm) | 13 |
| Max. drilling wood (mm) | 25 |
| Max. drilling masonry (mm) | 13 |
| Chuck capacity (mm) | 13 |