

RJS750-G

500W Jigsaw

Features

- Most visible cut line delivered by slim profile and AIRFORWARDS to remove dust
- High accuracy achieved through PRO STROKE mechanisms and LINEASSIST
- Quick Lock one finger blade clamp allows user to change blade easily
- Most compact and comfortable jigsaw with ergonomic handle and detachable vacuum port



SPECIFICATION (1)	RJS750-G
Sound pressure level (dB(A))	85.5
Sound pressure level uncertainty [dB[A]]	3
Sound power level measured [dB[A]]	96.5
Sound power level measured uncertainty [dB[A]]	3
Vibration cutting metal [m s ²]	5.1
Vibration cutting metal uncertainty [m s ²]	1.5
Vibration cutting in boards [m s ²]	4.3
Vibration cutting boards uncertainty [m s ²]	1.5
No load speed (rpm)	0-3,000
Supplied in	Recyclable Carton
Article Number	5133002216
Weight (kg)	1.8
Power input (W)	500
Max. cutting capacity wood (mm)	75
Max. cutting capacity steel (mm)	6
Stroke length (mm)	19