



# Product data sheet

Power tools for trade & industry

Jigsaw

## GST 90 BE Professional



\* Price including VAT

Top-class convenience in the entry level class

### The most important data

Rated power input	650 W
Cutting depth in wood	90 mm
Cutting depth in aluminium	20 mm

**Part number:** 0 601 58F 000

[> More product information](#)

## Technical Data

### Battery and power

Rated power input	650 W
-------------------	-------

### Performance data

Stroke rate at no load	500 – 3.100 spm
Cable length	2.5 m
Stroke height	26 mm

### Size and weight

Weight	2,6 kg
--------	--------

### Cutting depth

Cutting depth in wood	90 mm
Cutting depth in aluminium	20 mm
Cutting depth in non-alloyed steel	10 mm

## Noise/vibration information

### Sawing wood

Vibration emission value ah	6,0 m/s <sup>2</sup>
Uncertainty K	1,5 m/s <sup>2</sup>

### Sawing sheet metal

Vibration emission value ah	6,0 m/s <sup>2</sup>
Uncertainty K	1,5 m/s <sup>2</sup>

### Noise

Sound pressure level	84 dB(A)
Sound power level	95 dB(A)
Uncertainty K	1.5 dB

**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

---

## Advantages

- The reliable partner for day-to-day use
- High level of convenience with Bosch SDS for easy, tool-free saw blade changes
- Powerful 650 watt motor for fast work progress
- Improved saw blade clamping system for high cutting precision
- Bend-resistant steel base plate
- Exemplary smooth running when cutting, which ensures best results and low user fatigue

