

Product information

71 22 200 T

KNIPEX CoBolt®

Compact Bolt Cutters



MM  20°



Clever muscle man

- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport
- With slim multi-component grips without collar for better handling and easier transport
- Pliers with tether attachment point for mounting a fall protection
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- 20° angled head with joint bar on one side and side cutter for almost flush cutting, with space for gripping
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened

General

Article No.	71 22 200 T
EAN	4003773080053
Pliers	black atramentized
Handles	with slim multi-component grips, with integrated tether attachment point for a tool tether
weight	370 g
Dimensions	200 x 55 x 23 mm
Reach	no
RohS	no

Technical details

Style	2
Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm
Drop Protection System	yes

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAC440c002
UNSPSC 13.1	27111512

technical change and errors excepted



20° angled head with single-sided joint bar and diagonal cutting edge for flush cutting; with space for gripping

