

## Product information

# 71 31 250

## KNIPEX CoBolt® XL

Compact Bolt Cutters



The compact bolt cutters from KNIPEX now also available with long handles for one and two-hand operation.

Up to a 40-fold increase of manual force.

- For powerful cutting of larger cross-sections as well as very hard materials
- Two-hand operation for maximum cutting force
- Blades with recess for easier cutting of larger cross-sections thanks to better leverage close to the fulcrum
- 60 % less effort required compared to conventional high-leverage diagonal cutters
- 40-fold increase of manual force due to special joint design
- With gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm
- Induction-hardened precision blades: cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



### General

Article No.	71 31 250
EAN	4003773079644
Pliers	black atramentized
Handles	plastic coated
weight	475 g
Dimensions	250 x 53 x 20 mm
Reach	yes
RohS	no

### Technical details

Cutting capacities medium hard wire (diameter)	Ø 6.0 mm
Cutting capacities hard wire (diameter)	Ø 4.3 mm
Cutting capacities piano wire (diameter)	Ø 4.2 mm

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAC440c002
UNSPSC 13.1	27111512

technical change and errors excepted



two-hand operation for maximum cutting force

