

## Product information

# 73 05 160 T

### KNIPEX X-Cut®

#### Compact Diagonal Cutter

DIN ISO 5749



- Cuts finest strands as well as multi-core cables and piano wires
- Powerful, light and universal
- Pliers with tether attachment point for mounting a fall protection
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Box-joint design: highest stability with low weight
- Doubly supported joint axis for heavy duty
- Large opening width for thicker cables
- Cuts precisely, even through fine copper wires
- Compact, low-weight construction
- Universally usable, in the assembly, maintenance and production
- 40% less force required compared with standard diagonal cutters of the same length
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



### General

Article No.	73 05 160 T
EAN	4003773080077
Pliers	chrome plated
Head	chrome plated
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
weight	180 g
Dimensions	160 x 55 x 23 mm
Standard	DIN ISO 5749
Reach	no
RohS	no

### Technical details

Cutting capacities soft wire (diameter)	Ø 4.8 mm
Cutting capacities medium hard wire (diameter)	Ø 3.8 mm
Cutting capacities hard wire (diameter)	Ø 2.7 mm
Cutting capacities piano wire (diameter)	Ø 2.2 mm
Cutting capacity copper cable, multiple-stranded	Ø 12.0 mm
Drop Protection System	yes

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted

