

Product information

87 02 300 T

KNIPEX Cobra®

Hightech Water Pump Pliers

DIN ISO 8976



- Pliers with tether attachment point for mounting a fall protection
- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	87 02 300 T
EAN	4003773080169
Pliers	grey atramentized
Head	polished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
weight	600 g
Dimensions	300 x 64 x 25 mm
Standard	DIN ISO 8976
Reach	no
RohS	no

Technical details

Adjustment positions	30
Capacities for nuts	Ø 2 3/4
Capacities for nuts	60 mm
Capacities for pipes (diameter)	Ø 70 mm
Drop Protection System	yes

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112

technical change and errors excepted



