

# Product Specification PDF

Date	<b>Correct as of 2nd Aug 2019</b>
Brand	<b>C.K</b>
Product	<b>431013</b>
Description	<b>RedLine VDE Snipe Nose Plier 175mm</b>
Barcode	<b>5051074310132</b>
Commodity code	<b>8203200000</b>
Country of origin	<b>DE</b>



Features & Benefits	~ Two component, ergonomic design, with anti-slip horns for increased comfort, control & safety ~ Induction hardened jaws for outstanding long term performance ~ Cutting jaws with C.K optimised geometry for unsurpassed cutting performance ~ Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability ~ VDE approved ~ individually tested to 10,000V for safe live working up to 1,000V ~ Conforms to IEC 60900:2004 ; VDE0682/201 ; ISO 5745 ~ Cutting capacities: Hard: 1,4 mm / Medium hard: 2,0 mm / Soft: >4,0 mm ~ Total length: 175 mm
Applicable Standards	EN 60900 , VDE 682/2 1, ASTM-F 1505, ISO 5745
Health & Safety	None applicable
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	3	81
Width mm	60	65	80	300
Depth mm	25	30	250	430
Height mm	180	230	65	330
Weight	168	182	615	17.5
Packaging Information	Card use	0	Box	Case
	Card gms	0	69	900
	Plastic use	Hanger	0	-
	Plastic gms	14	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0