

Product Specification PDF

Date	Correct as of 11th May 2020
Brand	C.K
Product	T3778F
Description	Classic Oblique Cutter 120mm
Barcode	5013969687101
Commodity code	8203200000
Country of origin	DE



Features & Benefits ~ Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability ~ Precision box joint construction for permanent, adjustment free jaw alignment ~ Induction hardened jaws for outstanding long term performance ~ Mirror polished surface eliminates the risk of damage from flaking chrome ~ Spot welded double leaf springs for consistent, repetitive action ~ PVC handles for comfort & grip ~ Wide head, long jaws ~ Tapered head ~ Bevel: Full Flush Cut ~ Length of cutting edges: 18 mm ~ Overall length: 120 mm ~ Cutting capacities wire: Hard: 0,5 mm / Medium Hard: 1,2 mm / Soft: 1,6 mm

Applicable Standards

Health & Safety None applicable

Warranty C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	0	120
Width mm	73	60	0	380
Depth mm	18	25	0	300
Height mm	120	160	0	360
Weight	67	86	0	11.1
Packaging Information	Card use	Box	0	Case
	Card gms	18	0	787.5
	Plastic use	Bag	0	-
	Plastic gms	1	0	-
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0