
113A.12C 113A.C - Chromed adjustable wrenches





Description:

- Good access to the button = easy setting.
- Non-protruding moving jaw at maximum capacity.
- Pre-adjustment of jaw opening thanks to millimetric gradation.
- Right-hand button rotation.
- Range from 4" to 24".
- Presentation: chromed body and polished head faces.

A [mm]:	34
B [mm]:	80,0
C x C1 [mm]:	25,0 x 31,0
C1 [mm]:	31
E [mm]:	10,0
E1 [mm]:	18,0
E2 [mm]:	10,2
E3 [mm]:	13,0
E4 [mm]:	10,0
L [mm]:	306
L1 [mm]:	34
[g]:	700