

## JET.6MWB Heavy-duty mobile workbench



### Description:

- Lower the feet with the rotating handle to make your workbench as stable as a fixed workbench.
  - Its large 0.7 m<sup>2</sup> worktop in multilayered beech wood is coated with lint oil for stronger resistance to liquids and easier maintenance. You can install a vice on it.
  - Static resistance is 1-ton on the feet, 500 kg on the wheels.
  - Raise the feet with the rotating handle, the workbench is mobile again. This handle also allows moving the workbench easily.
  - 4 x 125 mm diameter wheels, 2 swivelling, 2 fixed.
  - 6 drawers compatible with XL modules, with aluminium handles and withstanding a load of 30 kg per drawer.
  - 1 large lateral compartment to store larger tools or objects, with shelf.
  - Single key for the drawers and compartment.
  - The left-hand side and back of the workbench can store the JETXL accessories (see FACOM catalogue).
  - The worktop is perforated for easy installation of a JET.A6M5 perforated panel.
  - Dimensions (L.x D.x H.): 1194 x 670 x 1002 mm.
- Weight: 127.8 kg