

JET.C4M3 JET+ 4-drawer chest - 3 modules per drawer**Description:**

- 4 drawers = 12 modules distributed in the 60 and 130 mm drawers:
- 3 drawers 60 mm high = 9 modules.
- 1 drawer 130 mm high = 3 modules.
- The 200 mm drawers can also be fitted with modules. (can be fitted with the JET2.15 and JET2.16 removable partitions - not supplied).
- Acceptable load and useful volume per drawer of M3 versions:
- 60mm drawer: 20 kg - 15 litres.
- 130mm drawer: 25 kg - 30 litres.
- Total load in the drawers: 85 kg.
- High storage capacity: 75 litres.
- Total load on the worktop in static position: 500 kg
- Overall dimensions (including wheels and worktop): L.774 x D.546 x H.480 mm.
- Drawer useful size: L.569 x D.421 x H.60 / 130 mm.

Color: Red 3020

[kg]: 45
