

JET.C4M4 JET+ 4-drawer chest - 4 modules per drawer**Description:**

- 4 drawers = 16 modules distributed in the 60 and 130 mm drawers:
- 3 drawers 60 mm high = 12 modules.
- 1 drawer 130 mm high = 4 modules.
- The 200 mm drawers can also be fitted with modules. (can be fitted with the JET2.15 and JET2.16 removable partitions - not supplied).
- Acceptable load and useful volume per drawer of M4 versions:
- 60 mm drawer: 25 kg - 20 litres.
- 130 mm drawer: 30 kg - 40 litres.
- Total load in the drawers: 105 kg.
- High storage capacity: 100 litres.
- Total load on the worktop in static position: 600 kg
- Overall dimensions (including wheels and worktop): L.964 x D.546 x H.480 mm.
- Drawer useful size: L.759 x D.421 x H.60 / 130 mm.

Color: Red 3020

[kg]: 51,50
