

JET.CR4GM3 JET+ 4-drawer roller cabinets - 3 modules per drawer**Description:**

- Ideal for mobile maintenance.
- Retractable handle for travelling.
- Easy handling thanks to its high performance wheels (diameter 125 mm, 2 fixed and 2 castors including one with brake).
- 4 drawers = 12 modules distributed in the 60 and 130 mm high drawers.
- 3 drawers 60 mm high = 9 modules.
- 1 drawer 130 mm high = 3 modules.
- The 200 mm drawers can also be fitted with modules.
- Can be fitted with the JET2.15 and JET2.16 removable partitions - not supplied
- Acceptable load and useful volume per drawer of M3 versions:
 - 60 mm drawer: 20 kg - 15 litres.
 - 130 mm drawer: 25 kg - 30 litres.
- Total load in the drawers: 85 kg.
- High storage capacity: 75 litres.
- Overall dimensions (including wheels and worktop): L.774 x D.546 x H.621 mm.
- Drawer useful size: L.569 x D.421 x H.60 / 130 mm.

Color: Black 9004

[kg]: 48,50
