

## JET.T7M3 JET+ 7-drawer mobile workbenches - 3 modules per drawer



### Description:

- 7 drawers (useful dimensions): 18 modules distributed in the 60 and 130 mm high drawers:
  - 5 drawers 60 mm high = 15 modules.
  - 1 drawers 130 mm high = 3 modules.
  - 1 drawer 200 mm high.
- Supplied with 6 partitions for 60 mm drawers and 2 partitions for 130 mm drawers.
- The 200 and 270 mm drawers can also be fitted with modules.
- Total load in the drawers: 155 kg.
- High storage capacity: 155 litres.
- 1 full-length closed compartment for storing long tools:
  - Door with key lock.
  - Identical key for the drawers and the compartment.
- Supplied with the plastic slider.
- For the wood top version, just add wood top JET.A14M5.
- Can be fitted with a JET.C4GM5 chest
- Compatible with the JET+ and JET.XL range of accessories.
- 4 very high performance wheels 160 mm diameter - 2 castors (including 2 with brakes) and 2 fixed.
- Overall dimensions (including wheels and worktop): L.1154 x D.546 x H.1000 mm.
- Drawer useful size: L.569 x D.421 x H.60/130/200 mm.
- Compartment dimensions: L.378 x D.430 x H. 679 mm (passage width with door open 310 mm).

---

**Color:** Red 3020

---

**[kg]:** 103

---