

NJ.3000F 3/8" titanium impact wrench



Description:

- Light weight titanium housing for maximum durability.
- Feather throttle for maximum operator control.
- Titanium exhaust deflector & muffler.
- Over molded comfort grip.
- One hand power & reverse adjustment.
- Innovative motor construction increases durability.
- Side fed air motor for maximum power delivering 710 N.m.
- Also available as a 1/2": NS.2000F
- Breakaway torque 710 N.m.
- Breakaway torque 570 N.m.
- Blows per minute 1750 cpm.
- Free speed 10500 tr/min.
- Square drive 3/8".
- Working pressure 6,2 bar.
- Average air consumption 125 l/min.
- Air inlet 1/4".
- Minimum hose diameter 10 mm - 3/8".
- Vibration 3,06 m/s²/a.
- Vibration 0,79 m/s²/K.
- Sound pressure 93,80 dB(A).
- Sound power 104,80 dB(A).

H [mm]:	180
L [mm]:	152
L1 [mm]:	66
[kg]:	1,300

