

R.8 R 1/4" drive metric 6-point sockets**Description:**

- OG V® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.
- Available as sets on metal rack (Ref R.40E).

A [mm]:	8,0
d [mm]:	12,0
d1 [mm]:	12,0
H3 [mm]:	6,50
L [mm]:	22
L1 [mm]:	6,5
Hex Size [mm]:	6
[g]:	11,50



