

## S.19 S - 1/2" metric 12-point sockets



### Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.
- Supplied on metal rack. Ref S.40E (8 --> 16 mm) and Ref S.41E (17 --> 24 mm).

|                |      |
|----------------|------|
| A [mm]:        | 19   |
| d [mm]:        | 24,6 |
| d1 [mm]:       | 26,6 |
| L [mm]:        | 36   |
| L1 [mm]:       | 14,0 |
| 12-Point [mm]: | 12   |
| [g]:           | 69   |

