

S.27 S - 1/2" metric 12-point sockets**Description:**

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.
- Supplied on metal rack. Ref S.40E (8 --> 16 mm) and Ref S.41E (17 --> 24 mm).

A [mm]:	27
d [mm]:	29,2
d1 [mm]:	36,6
L [mm]:	44
L1 [mm]:	19,0
12-Point [mm]:	12
[g]:	142

